



FRONT VIEW



SIDE VIEW



Click [here](#) for the 3D model.

Dimensions

D	14.5mm MAX
L	33mm MAX
LL	38mm MIN
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	300

General Information

Series	A70
Dielectric	Metallized Polypropylene
Style	Axial
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C. maxK0 = 320.

Specifications

Capacitance	3.3 uF
Capacitance Tolerance	20%
Voltage AC	90 VAC
Voltage DC	160 VDC, 120 VDC (105C)
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.06% 1kHz
Insulation Resistance	9.0909 GOhms
Max dV/dt	1V/us
Inductance	33 nH