



#### General Information

Style	Metal Sealed
Description	Metal Sealed Type Multilayer Piezoelectric Actuators
RoHS	With Exemptions
SCIP Number	c64eed42-9f3b-4f55-976e-a799ec5ecf68
Notes	Female thread type, V Groove.
REACH	SVHC (PZT - CAS 12626-81-2)

#### Specifications

Series	AHB
Displacement	103um +/-15um
Voltage DC	150 VDC
Capacitance	11 uF
Capacitance Tolerance	20%
Resonant Frequency	8 kHz
Generated Force	800 N
Insulation Resistance	5 MOhms
Temperature Range	-25/+85°C

Click [here](#) for the 3D model.

#### Dimensions

D	11.5mm +/-0.5mm
L	98.4mm +/-0.5mm
LL	142mm +/-5mm

#### Packaging Specifications

Typical Component Weight	61
Packaging	Tray
Packaging Quantity	10