



Click [here](#) for the 3D model.

Dimensions

D	40mm +/-1mm
L	45mm +/-2mm
S	20mm +/-0.1mm
LL	7.5mm +/-0.5mm
F	1.3mm

Packaging Specifications

Sleeving	true
Packaging	Tray

General Information

Series	ALP22
Dielectric	Aluminum Electrolytic
Style	Snap-In
Description	Solder Pin, Aluminum Electrolytic
RoHS	Yes
Lead	5 Pin Solder
AEC-Q200	No
Typical Component Weight	80 g
Notes	Dimensions D And L Include Sleeving.

Specifications

Capacitance	680 uF
Capacitance Tolerance	20%
Voltage DC	200 VDC, 230 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	26000 Hrs
Leakage Current	816 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.