


General Information

Series BEAD L

Style Through-Hole

RoHS Yes

[Click here for the 3D model.](#)
Dimensions

D 3.4mm +/-0.2mm

L 67mm +/-2mm

L2 4.4mm +/-0.2mm

F 0.65mm NOM

Specifications

Temperature Range -20/+70°C

Packaging Specifications

Packaging T&R

Packaging Quantity 5000

Typical Component Weight 400 mg

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.