

B-01-ATF

Aliases (UDLB00001ATF00)

Differential Mode Chokes - Signal, KEMET, BEAD L, Through-Hole, Normal Mode

ø3.4±0.2	4.4±0.2	ø0.65 (Tin coated soft cop	per wire)
•	67+2 0		

General Information	
Series	BEAD L
Style	Through-Hole
RoHS	Yes

Click here for the 3D model.

Dimensions	
D	3.4mm +/-0.2mm
L	67mm +/-2mm
L2	4.4mm +/-0.2mm
F	0.65mm NOM

Packaging Specifications			
Packaging	T&R		
Packaging Quantity	1500		
Typical Component Weight	400 mg		

Specifications	
Temperature Range	-20/+70°C

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/05/2025 © 2006 - 2025 YAGEO