



Click [here](#) for the 3D model.

#### General Information

Series	B-20
Style	Round - Toroidal
Cable Type	Round Cable
Description	EMI Core Beads, Single Piece Core
RoHS	Yes
Materials	Ni-Zn
Core	Ni-Zn Ferrite

#### Dimensions

D	2.5mm +/-0.3mm
D2	1mm +/-0.3mm
T	1.2mm +/-0.3mm

#### Specifications

Temperature Range	-25/+85°C
Effective Frequency	500 MHz (FM Band Range)

#### Packaging Specifications

Packaging	Bulk
Packaging Quantity	30000
Typical Component Weight	30 mg

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.