



General Information

Series	EFG2
Style	Sheet
Description	Flex Suppressor GHz Band High Performance Type
Features	GHz Band High Performance Type, Wi-Fi, GPS, LTE-A
RoHS	Yes
Qualifications	UL94 HB, UL File No. E176124
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Specifications

Temperature Range	-40/+105°C
Permeability	35 u At 3MHz
Effective Frequency	1 GHz to 10GHz
Specific Gravity	3.9 TYP
Thermal Conductivity	1.05 typical
Surface Resistivity	1 MOhm/sq. TYP

Dimensions

Sheet Size	80x80mm
L	80mm NOM
W	80mm NOM
T	0.2mm NOM

Packaging Specifications

Tape Thickness	0.03mm
Typical Component Weight	5.08 g