



General Information

Series	EFG3
Style	Sheet
Description	Flex Suppressor Flame Retardant Type
Features	Flame Retardant Type
RoHS	Yes
Qualifications	UL94 HB, UL File No. E176124
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Specifications

Temperature Range	-40/+105°C
Permeability	42 u At 3MHz
Effective Frequency	1 GHz to 10GHz
Specific Gravity	4.1 TYP
Thermal Conductivity	1.43 typical
Surface Resistivity	1 MOhm/sq. TYP

Dimensions

Sheet Size	240x240mm
L	240mm NOM
W	240mm NOM
T	0.3mm NOM

Packaging Specifications

Typical Component Weight	69.12 g
--------------------------	---------