



General Information

Series	EFX
Style	Sheet
Description	Flex Suppressor Halogen Free Type
Features	High Magnetic Permeability
RoHS	Yes
Qualifications	UL94 HB, UL File No. E176124
Environment	Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Specifications

Temperature Range	-40/+105°C
Permeability	100 u At 3MHz
Effective Frequency	10 GHz MAX
Specific Gravity	3.2 Atm TYP
Thermal Conductivity	0.22 W/m K

Dimensions

Sheet Size	240x240mm
L	240mm
W	240mm
T	0.1mm +/-0.05mm

Packaging Specifications

Tape Description	Without PET Tape (Txx00)
Tape Thickness	0.03mm