



Click [here](#) for the 3D model.

#### General Information

Series	ESD-FPD
Style	Flat - Split
Cable Type	Flat Cable
Description	EMI Core Split, For Flat Cables With Metal Clamp
Features	Stainless Steel Clamp
RoHS	Yes
Applicable Cable	50 Core
Materials	Ni-Zn

#### Dimensions

L	80mm +/-1mm
T	12.7mm +/-1mm
H	10mm +/-2mm
A	68.6mm +/-1mm
B	2.6mm +/-1mm

#### Specifications

Temperature Range	-25/+85°C
Effective Frequency	500 MHz (FM Band Range)

#### Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	240
Typical Component Weight	42.48 g