



Click [here](#) for the 3D model.

#### General Information

Series	ESD-FPL
Style	Flat - Solid
Cable Type	Flat Cable
Description	EMI Core Solid, For Flat Cables, Bare Type
RoHS	Yes
Applicable Cable	8 Core
Materials	Ni-Zn

#### Dimensions

L	16mm +/-0.5mm
T	12mm +/-0.4mm
H	4.5mm +/-0.3mm
A	11.5mm +/-0.3mm
B	0.85mm +/-0.15mm

#### Specifications

Temperature Range	-25/+85°C
Effective Frequency	500 MHz (FM Band Range)

#### Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	1650
Typical Component Weight	3.4 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.