



Click [here](#) for the 3D model.

#### Dimensions

D	110mm MAX
D2	58.5mm +/-1mm
T	26mm MAX

#### Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	12
Typical Component Weight	615 g

#### General Information

Series	ESD-R-NC
Style	Round - Toroidal
Cable Type	Round Cable
Description	EMI Core Solid, Large-Size Ring Type, For Round Cables
Features	Low and High Frequency Range, Flame Retardancy
RoHS	Yes
SCIP Number	d5c28613-591c-4483-83c1-5d29064c1b21
Qualifications	UL94V-0
Case Color	Black with yellow tape
Materials	Nanocrystal

#### Specifications

Temperature Range	-40/+120°C
Effective Frequency	10 MHz (AM Band Range) or 500 MHz (FM Band Range)