


ESD-R-12D

Aliases (UECESDR12D0000)

KEMET, ESD-R, EMI Cores, Noise Suppression



Click [here](#) for the 3D model.

Dimensions

D	12.9mm +/-1.0mm
D2	6mm +/-1.0mm
T	6.4mm +/-1.0mm

Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	2000
Typical Component Weight	2.4 g

General Information

Series	ESD-R
Style	Round - Toroidal
Cable Type	Round Cable
Description	EMI Core Solid, For Round Cables, Toroidal Cores With Case
RoHS	Yes
Qualifications	UL94 V-2
Case Color	Black
Toroidal	ESD-R-12S
Materials	Ni-Zn

Specifications

Temperature Range	-25/+85°C
Effective Frequency	500 MHz (FM Band Range)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.