


Click [here](#) for the 3D model.

**General Information**

Series	ESD-R-NC
Style	Round - Toroidal
Cable Type	Round Cable
Description	EMI Core Solid, Large-Size Ring Type, For Round Cables
Features	Low and High Frequency Range, Flame Retardancy
RoHS	Yes
Qualifications	UL94V-0
AEC-Q200	No
Case Color	Black
Materials	Nanocrystal
Core	Nanocrystal

**Dimensions**

D	131mm MAX
D2	74mm MIN
L	181mm MAX
T	26mm MAX
L2	150mm +/-0.5mm

**Specifications**

Temperature Range	-40/+130°C
Effective Frequency	10 MHz (AM Band Range) or 500 MHz (FM Band Range)

**Packaging Specifications**

Packaging	Tray, Box
Packaging Quantity	9
Typical Component Weight	560 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.