



Click [here](#) for the 3D model.

#### General Information

Series	ESD-R-SR
Style	Round - Toroidal
Cable Type	Round Cable
Description	EMI Core Solid, Large-Size Ring Type, For Round Cables, Coated Type
Features	High Impedance, Effectively Suppresses Radiation at 150 kHz, Low Frequency Noise
RoHS	Yes
Qualifications	UL94 V-2
Case Color	Gray
Materials	Mn-Zn
Core	Mn-Zn Ferrite

#### Specifications

Temperature Range	-25/+85°C
Effective Frequency	10 MHz (AM Band Range)

#### Dimensions

D	48.5mm MAX
D2	26mm MIN
T	16mm MAX

#### Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	100
Typical Component Weight	84.3 g