


ESD-R-57SR-P

Aliases (UECESDR57SRP00)

Specification

EMI Suppression, KEMET, ESD-R-SR, Round - Toroidal, Noise Suppression





	I .
(Click here for the 3D model.

General Information				
Series	ESD-R-SR			
Style	Round - Toroidal			
Cable Type	Round Cable			
Description	EMI Core Solid, Large-Size Ring Type, For Round Cables, Coated Type			
Features	High Impedance, Effectively Suppresses Radiation at 150 kHz, Low Frequency Noise			
RoHS	Yes			
Qualifications	UL94 V-2			
AEC-Q200	No			
Case Color	Gray			
Materials	Mn-Zn			
Core	Mn-Zn Ferrite			

Dimensions		
D	59mm MAX	
D2	34mm MIN	
Т	21mm MAX	

Specifications	
Temperature Range	-25/+85°C
Effective Frequency	10 MHz (AM Band Range)

Packaging Specifications				
Packaging	Tray, Box			
Packaging Quantity	60			
Typical Component Weight	141.5 g			

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/05/2025 © 2006 - 2025 YAGEO