



Click [here](#) for the 3D model.

Dimensions

| | |
|----|---------------|
| D | 61mm MAX |
| D2 | 33.2mm +/-1mm |
| T | 25mm MAX |

Packaging Specifications

| | |
|--------------------------|-----------|
| Packaging | Tray, Box |
| Packaging Quantity | 60 |
| Typical Component Weight | 186 g |

General Information

| | |
|----------------|--|
| Series | ESD-R-NC |
| Style | Round - Toroidal |
| Cable Type | Round Cable |
| Description | EMI Core Solid, Large-Size Ring Type, For Round Cables |
| Features | Low and High Frequency Range, Flame Retardancy |
| RoHS | Yes |
| SCIP Number | d5c28613-591c-4483-83c1-5d29064c1b21 |
| Qualifications | UL94V-0 |
| Case Color | Black with yellow tape |
| Materials | Nanocrystal |

Specifications

| | |
|---------------------|---|
| Temperature Range | -40/+120°C |
| Effective Frequency | 10 MHz (AM Band Range) or 500 MHz (FM Band Range) |