



#### General Information

Series	ESTV
Description	Flex Suppressor Halogen Free Type
Features	Resonance suppression
RoHS	Yes
Qualifications	UL94 V-0, UL File No. E176124
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

#### Specifications

Temperature Range	-40/+105°C
Permeability	100 $\mu$ At 3MHz
Effective Frequency	1 MHz to 3GHz
Specific Gravity	3.1 TYP
Surface Resistivity	1 M $\Omega$ m/sq. TYP

#### Dimensions

L	10000mm NOM
W	9mm NOM
T	0.05mm NOM

#### Packaging Specifications

Tape Thickness	0.03mm
Typical Component Weight	25 g