



Click [here](#) for the 3D model.

Dimensions	
L	18mm -0.5mm
H	14.5mm -0.5mm
T	7.5mm -0.5mm
S	15mm +/-0.4mm
LL	16.5mm +0.5mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	400

General Information	
Series	SMR/F211
Dielectric	Metallized PPS
Style	Radial
Features	Audio Applications
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	2.7 g
Miscellaneous	The rated voltage decreases 2%/C between +125C and +150C.
Notes	Case Size = BL.

Specifications	
Capacitance	3.3 uF
Capacitance Tolerance	5%
Voltage AC	30 VAC
Voltage DC	50 VDC
Temperature Range	-55/+150°C
Rated Temperature	125°C
Dissipation Factor	0.15% 1kHz
Insulation Resistance	1.515 GOhms
Max dV/dt	6 V/us