



Click [here](#) for the 3D model.

Dimensions

A	49.5mm MIN
B	185mm MIN
D1	Threaded Studs M10

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

General Information

Series	FLLDU
Style	Feed-Through Filter
Description	Power Feed-Through Filters
Features	Industrial, Medical
RoHS	Yes
Qualifications	UL

Specifications

Voltage AC	440 VAC
Voltage DC	750 VDC
Rated Frequency	50-60 Hz
Rated Current	200 A
Rated Temperature	40°C
Temperature Range	-40/+85°C
Climate Category	40/085/56