


## FLLE2025ASDI

Aliases (LLE2025ASDI)

KEMET, FLLE2-S, EMI/RFI Filters, Noise Suppression, 300 VAC, 300 V, 25 A, 130.5x56.5x48.5mm



Click [here](#) for the 3D model.

### Dimensions

L	130.5mm MIN
W	56.5mm MIN
H	48.5mm MIN
Lead	Threaded Studs M4

### Packaging Specifications

Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	720 g

### General Information

Series	FLLE2-S
Style	Chassis Mount
Description	Single Phase, Chassis Mount Filters
Features	Single Phase
Phase	Single-phase
RoHS	Yes
Qualifications	IEC/EN 60939, UL, CSA
Lead	Threaded Studs M4
Terminal Type	Threaded Studs M4

### Specifications

Voltage AC	300 VAC
Voltage DC	300 VDC
Rated Frequency	50-60 Hz
Rated Current	25 A
Ripple Current	25 A
Rated Temperature	40°C
Temperature Range	-25/+100°C
Climate Category	25/100/21
Leakage Current	0.37 mA (MAX)
Test Voltage DC (P/N to E)	2250 VDC
Test Voltage DC (P to N)	1300 VDC