



Click [here](#) for the 3D model.

## General Information

Series	GF
Style	Metal Box
Description	Noise Filters
RoHS	With Exemptions
SCIP Number	d9c7b340-5c0a-4e16-b4ef-391381f88890
Qualifications	UL
AEC-Q200	No
Miscellaneous	30 K Self-Temperature Rise Max.
Terminal Type	Screw

## Dimensions

L	70mm NOM
W	53mm
H	29mm

## Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	10
Typical Component Weight	150 g

## Specifications

Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	20 A (AC/DC)
Ripple Current	20 A (AC/DC)
Rated Temperature	55°C
Temperature Range	-20/+60°C
Leakage Current	1 mA
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.