


GF-220U

Aliases (UNFGF220UXXXXX)

Obsolete

EMI Filters, KEMET, GF, Metal Box, Noise Suppression



General Information			
Series		GF	
Style		Metal Box	
Descri	ption	Noise Filters	
RoHS		With Exemptions	
SCIP N	Number	d9c7b340-5c0a-4e16-b4ef-3913 81f88890	
Qualifi	ications	UL	
AEC-C	2200	No	
Miscel	laneous	30 K Self-Temperature Rise Max.	
Termir	nal Type	Screw	

Click here for the 3D model.

Dimensions			
L	70mm NOM		
W	53mm		
Н	29mm		

Packaging Specifications			
Packaging	Tray, Box		
Packaging Quantity	10		
Typical Component Weight	150 g		

Specifications	
Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	20 A (AC/DC)
Ripple Current	20 A (AC/DC)
Rated Temperature	55°C
Temperature Range	-20/+60°C
Leakage Current	1mA
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/06/2025 © 2006 - 2025 YAGEO