



Click [here](#) for the 3D model.

**General Information**

Series	GL
Style	Metal Box
Description	Noise Filters
RoHS	Yes
Qualifications	UL, CSA, TUV
Miscellaneous	30 K Self-Temperature Rise Max.

**Specifications**

Voltage AC	250 VAC
Rated Current	3 A (AC/DC)
Ripple Current	3 A (AC/DC)
Rated Temperature	55°C
Temperature Range	-25/+55°C
Leakage Current	0.5 mA MAX (250 V 60 Hz)

**Dimensions**

L	67mm NOM
W	52mm NOM
H	26mm NOM

**Packaging Specifications**

Packaging	Tray, Box
Packaging Quantity	25
Typical Component Weight	55 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.