


GT-2200

Aliases (UNFGT2200XXXXX)

Obsolete

KEMET, GT, EMI/RFI Filters, Noise Suppression, 250 VAC, 20 A



Click [here](#) for the 3D model.

General Information

Series	GT
Style	Metal Box
Description	Noise Filters
RoHS	With Exemptions
Miscellaneous	35 K Self-Temperature Rise Max.
Lead	Screw Terminals
Terminal Type	Screw

Specifications

Voltage AC	250 VAC
Rated Current	20 A (AC/DC)
Ripple Current	20 A (AC/DC)
Temperature Range	-25/+55°C
Leakage Current	0.5 mA MAX (250 V 60 Hz)

Dimensions

L	84mm NOM
W	50.8mm NOM
H	39mm NOM
Lead	Screw Terminals

Packaging Specifications

Packaging	Tray
Packaging Quantity	10
Typical Component Weight	270 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.