



Click [here](#) for the 3D model.

Dimensions

L	84mm NOM
W	50.8mm NOM
H	39mm NOM
Lead	Screw Terminals

Packaging Specifications

Packaging	Tray
Packaging Quantity	10
Typical Component Weight	270 g

General Information

Series	GT
Style	Metal Box
Description	Noise Filters
RoHS	With Exemptions
SCIP Number	97462fd0-8e28-4245-8658-d38f8b19fa11
Qualifications	UL, TUV
Notes	Last time buy due: May 31, 2024.
Miscellaneous	35 K Self-Temperature Rise Max.
Lead	Screw Terminals
Terminal Type	Screw

Specifications

Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	20 A (AC/DC)
Temperature Range	-25/+55°C
Leakage Current	0.5 mA MAX (250 V 60 Hz)
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground