



Click [here](#) for the 3D model.

General Information

Series	KHB DISC Comm Y5P HV
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Wire Leads
Failure Rate	N/A
AEC-Q200	No

Dimensions

D	12.5mm MAX
T	4.5mm MAX
S	5mm NOM
LL	25mm +/-1mm
F	0.6mm +/-0.1mm

Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------

Specifications

Capacitance	4,700 pF
Capacitance Tolerance	10%
Voltage DC	1000 VDC
Dielectric Withstanding Voltage	2,000 VDC
Temperature Range	-30/+85°C
Temperature Coefficient	Y5P