



Click [here](#) for the 3D model.

#### Dimensions

|   |            |
|---|------------|
| L | 38mm NOM   |
| W | 30mm NOM   |
| H | 22.5mm NOM |

#### Packaging Specifications

|                          |           |
|--------------------------|-----------|
| Packaging                | Tray, Box |
| Packaging Quantity       | 50        |
| Typical Component Weight | 30 g      |

#### General Information

|                |                                 |
|----------------|---------------------------------|
| Series         | MA                              |
| Style          | Plastic Box                     |
| Description    | Noise Filters                   |
| RoHS           | Yes                             |
| Qualifications | UL, CSA, TUV                    |
| Miscellaneous  | 30 K Self-Temperature Rise Max. |

#### Specifications

|                   |  |
|-------------------|--|
| Voltage AC        | 250 VAC  |
| Voltage           | 1500 VAC Withstanding Voltage 1 Min. Line to Ground    |
| Rated Current     | 4 A (AC/DC)  |
| Ripple Current    | 4 A (AC/DC)  |
| Temperature Range | -25/+55°C  |
| Leakage Current   | 0.75 mA  |
| ESR               | 300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground |