



Click [here](#) for the 3D model.

#### Dimensions

D	45mm NOM
L	53.5mm NOM

#### Packaging Specifications

Typical Component Weight	240
Packaging	Bulk Tray, Box
Packaging Quantity	30

#### General Information

Style	Bolt-On
Description	Langevin Bolt-On Transducers
RoHS	With Exemptions
SCIP Number	6629125f-50d3-4e75-ae76-25e0bc1955b0
Notes	Horn construction; output surface has step or horn shape.

#### Specifications

Series	NBL
Capacitance	4000 pF
Resonant Frequency	40.2 kHz
Dynamic Admittance	15 mS
Mechanical Q	500 Qm
Allowable Velocity	50 cm/S
Allowable Power	50
Temperature Range	-40/+120°C