



Click [here](#) for the 3D model.

Dimensions	
L	13.5mm MAX
H	7.5mm MAX
T	3.9mm MAX
S	7.5mm +0.6/-0.1mm
H0	16mm +/-0.5mm
F	0.6mm +/-0.05mm

Packaging Specifications	
Packaging	Ammo, 330x330x50mm, Box
Packaging Quantity	800

General Information	
Series	PME271Y/P271
Dielectric	Metallized Paper
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Formed To 7.5mm
Safety Class	Y2
Qualifications	ENEC, UL, cUL, CQC
AEC-Q200	No
Construction	Molded
Miscellaneous	SRF= 37 MHz.

Specifications	
Capacitance	2200 pF
Capacitance Tolerance	20%
Voltage DC	1000 VDC
Voltage AC	250 VAC (Y2)
Temperature Range	-40/+100°C
Rated Temperature	100°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	2000 V/us