



Click [here](#) for the 3D model.

### Dimensions

|   |            |
|---|------------|
| L | 23.6mm MAX |
| W | 4mm MAX    |
| T | 1.9mm MAX  |

### Packaging Specifications

|                          |                |
|--------------------------|----------------|
| Typical Component Weight | 1.2            |
| Packaging                | Bulk Tray, Box |
| Packaging Quantity       | 1000           |

### General Information

|             |                                           |
|-------------|-------------------------------------------|
| Style       | Rubber Cased                              |
| Description | Multilayer Piezoelectric Bimorph Actuator |
| RoHS        | With Exemptions                           |
| SCIP Number | 96933f00-7dd0-4e6d-8a13-be939072857c      |
| REACH       | SVHC (PZT - CAS 12626-81-2)               |

### Specifications

|                         |                |
|-------------------------|----------------|
| Series                  | R11            |
| Capacitance             | 1 uF           |
| Capacitance Tolerance   | 20%            |
| Maximum Driving Voltage | 25 V Peak-Peak |
| Resonant Frequency      | 6 kHz          |
| Temperature Range       | -25/+70°C      |