



Click [here](#) for the 3D model.

Dimensions

L	23.6mm MAX
W	4mm MAX
T	1.9mm MAX

Packaging Specifications

Typical Component Weight	1.2
Packaging	Bulk Tray, Box
Packaging Quantity	1000

General Information

Style	Rubber Cased
Description	Multilayer Piezoelectric Bimorph Actuator
RoHS	With Exemptions
SCIP Number	96933f00-7dd0-4e6d-8a13-be939072857c
REACH	SVHC (PZT - CAS 12626-81-2)

Specifications

Series	R11
Capacitance	1 μ F
Capacitance Tolerance	20%
Maximum Driving Voltage	25 V Peak-Peak
Resonant Frequency	6 kHz
Temperature Range	-25/+70°C