



Click [here](#) for the 3D model.

**General Information**

Style	Rubber Cased
Description	Multilayer Piezoelectric Bimorph Actuator
RoHS	With Exemptions
SCIP Number	96933f00-7dd0-4e6d-8a13-be939072857c
REACH	SVHC (PZT - CAS 12626-81-2)

**Specifications**

Series	R11
Capacitance	1 uF
Tolerance	20%
Maximum Driving Voltage	25 V Peak-Peak
Resonant Frequency	6 kHz
Temperature Range	-25/+70°C

**Dimensions**

L	23.6mm MAX
W	4mm MAX
T	1.9mm MAX

**Packaging Specifications**

Typical Component Weight	1.2
Packaging	Bulk Tray, Box
Packaging Quantity	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.