

No Drawing Available.

Dimensions	
Sheet Size	220x185mm
L	220mm NOM
W	185mm NOM
T	0.2mm NOM

Packaging Specifications	
Tape Description	Without PET Tape (Txx00)
Tape Thickness	0.03mm
Typical Component Weight	30.96 g

General Information	
Series	RM4A
Style	Sheet
Description	Flex Suppressor Magnetic Sheet For RFID
Features	High Magnetic Permeability Type, Low Magnetic Loss Type
RoHS	Yes
Environment	Halogen Free, PVC Free, Lead Free, RoHS Compliant

Specifications	
Temperature Range	-40/+85°C
Permeability	50 $\mu$ At 13.56MHz
Effective Frequency	13.56 MHz and below
Specific Gravity	3.6 TYP
Surface Resistivity	10 MOhm/sq. TYP

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.