



Click [here](#) for the 3D model.

#### Dimensions

D	7mm MAX
L	10.5mm MAX
S	4mm +/-0.5mm
F	0.6mm NOM

#### Packaging Specifications

Typical Component Weight	890 mg
Packaging	Bulk
Packaging Quantity	8000

#### General Information

Series	SBC2
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Miscellaneous	Pin Lead Terminal

#### Specifications

Inductance	100 uH
Inductance Tolerance	10%
Temperature Range	-20/+105°C
Shielded	false
Current	0.67 Amps
DC Resistance	0.41 Ohms