

## SBC4-221-721

Aliases (UPIN4221721000)

KEMET, SBC4, Ferrite, 10%, 220 uH, 9mm, 5mm



Click [here](#) for the 3D model.

### Dimensions

D	9mm MAX
L	14.5mm MAX
S	5mm +/-0.5mm
F	0.6mm NOM

### Packaging Specifications

Typical Component Weight	2.49 g
Packaging	Bulk
Packaging Quantity	4000

### General Information

Series	SBC4
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Miscellaneous	Pin Lead Terminal

### Specifications

Inductance	220 uH
Inductance Tolerance	10%
Temperature Range	-20/+105°C
Shielded	No
Current	0.72 Amps
DC Resistance	0.47 Ohms