



Click [here](#) for the 3D model.

Dimensions

D	9mm MAX
L	12mm MAX
S	5.5mm NOM
F	0.45mm NOM

Packaging Specifications

Typical Component Weight	2.4 g
Packaging	Bulk
Packaging Quantity	3000

General Information

Series	SBC4
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Miscellaneous	Soft Lead Terminal

Specifications

Inductance	33 uH
Inductance Tolerance	20%
Temperature Range	-20/+105°C
Shielded	false
Current	1.8 Amps
DC Resistance	0.09 Ohms