



Click [here](#) for the 3D model.

#### Dimensions

D	15mm MAX
L	19mm MAX
S	10mm NOM
F	1.4mm NOM

#### Packaging Specifications

Typical Component Weight	10 g
Packaging	Bulk
Packaging Quantity	900

#### General Information

Series	SBC8
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Miscellaneous	Soft Lead Terminal

#### Specifications

Inductance	4700 nH
Inductance Tolerance	20%
Temperature Range	-20/+105°C
Shielded	false
Current	9.2 Amps
DC Resistance	0.01 Ohms