


SBC9-221-821

Aliases (UPIN9221821000)

KEMET, SBC9, Ferrite, 10%, 220 uH, 12mm, 8.5mm



Click [here](#) for the 3D model.

Dimensions

D	12mm MAX
L	12mm MAX
S	8.5mm NOM
F	0.35mm NOM

Packaging Specifications

Typical Component Weight	4.5 g
Packaging	Bulk
Packaging Quantity	2000

General Information

Series	SBC9
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Miscellaneous	Soft Lead Terminal

Specifications

Inductance	220 uH
Inductance Tolerance	10%
Temperature Range	-20/+105°C
Shielded	No
Current	0.82 Amps
DC Resistance	0.41 Ohms