



Click [here](#) for the 3D model.

General Information

Series	SBCP-14HY
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads

Dimensions

D	12mm MAX
L	15mm MAX
S	5mm +/-0.5mm
F	0.6mm NOM

Packaging Specifications

Typical Component Weight	6 g
Packaging	Bulk
Packaging Quantity	1500

Specifications

Inductance	2.2 uH (0.01 MHz)
Inductance Tolerance	30%
Inductance	2,200 nH
Temperature Range	-20/+105°C
Shielded	No
Current	4.35 Amps
DC Resistance	20 mOhms
DC Resistance	0.02 Ohms