



Click [here](#) for the 3D model.

#### General Information

Series	SBCP-47HY
Style	Through-Hole Drum
Core	Ferrite
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads

#### Dimensions

D	5mm MAX
L	7.5mm MAX
H	18mm +2mm
S	2.5mm +/-0.5mm
F	0.5mm NOM

#### Packaging Specifications

Typical Component Weight	500 mg
Packaging	Bulk
Packaging Quantity	6000

#### Specifications

Inductance	680 uH (0.01 MHz)
Inductance Tolerance	10%
Inductance	680 uH
Temperature Range	-20/+105°C
Shielded	false
Current	0.19 Amps
DC Resistance	3.5 Ohms
DC Resistance	3.5 Ohms