



Click [here](#) for the 3D model.

### Dimensions

D	24.5mm MAX
T	22mm MAX
H	27.5mm MAX
LL	3.8mm +/-1mm
S	8mm NOM
S1	15mm NOM
Wire Size	0.5mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	16.1 g

### General Information

Series	SC Three Phase
Style	Through-Hole
Features	High Impedance
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 15 K.
Core	Mn-Zn Ferrite

### Specifications

Voltage AC	250 VAC
Voltage DC	250 VDC
Inductance	0.7 mH (10 kHz)
Current	1 A
Temperature Range	-25/+120°C
DC Resistance	38 mOhms