



Click [here](#) for the 3D model.

Dimensions	
D	34mm MAX
T	23mm MAX
LL	15mm +/-2mm
S	7mm
S1	20mm
Wire Size	0.6mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	200
Typical Component Weight	25 g

General Information	
Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	8 mH (100 kHz)
Current	2 A
Temperature Range	-40/+105°C
DC Resistance	150 mOhms