



Click [here](#) for the 3D model.

#### General Information

Series	SC-J
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 70 K.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Inductance	12 mH (10 kHz)
Current	2 A
Temperature Range	-40/+120°C
DC Resistance	180 mOhms

#### Dimensions

D	24mm MAX
T	16mm MAX
H	25mm MAX
LL	3.5mm +/-1.5mm
S	13mm NOM
S1	11mm NOM
Wire Size	0.55mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	150
Typical Component Weight	13 g