



Click [here](#) for the 3D model.

#### Dimensions

|           |              |
|-----------|--------------|
| D         | 17mm MAX     |
| T         | 17mm MAX     |
| H         | 14.5mm MAX   |
| LL        | 3.6mm +/-1mm |
| S         | 8mm NOM      |
| S1        | 13mm NOM     |
| Wire Size | 0.5mm        |

#### Packaging Specifications

|                          |      |
|--------------------------|------|
| Packaging                | Tray |
| Packaging Quantity       | 280  |
| Typical Component Weight | 6 g  |

#### General Information

|               |   |
|---------------|---|
| Series        | SC_JKH                                      |
| Style         | Through-Hole                                |
| RoHS          | Yes   |
| Notes         | Lead Spacing (S/S1) Are For Reference Only. |
| Miscellaneous | Temperature Rise Maximum: 40 K.             |
| Core          | Mn-Zn Ferrite                               |

#### Specifications

|                   |            |
|-------------------|------------|
| Voltage AC        | 250 VAC    |
| Inductance        | 3 mH       |
| Current           | 2 A        |
| Temperature Range | -25/+120°C |
| DC Resistance     | 85 mOhms   |