



#### General Information

Series	SC-JH
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 60 K.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Inductance	10.99 mH (100 kHz)
Current	3 A
Temperature Range	-40/+120°C
DC Resistance	42 mOhms

Click [here](#) for the 3D model.

#### Dimensions

D	31mm MAX
T	32mm MAX
H	15mm MAX
LL	3.5mm +/-1mm
S	25mm NOM
S1	27.5mm NOM
Wire Size	0.7mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	180
Typical Component Weight	26.5 g