



Click [here](#) for the 3D model.

General Information

Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 75 K.
Core	Mn-Zn Ferrite

Dimensions

D	34mm MAX
T	23mm MAX
LL	15mm +/-2mm
S	18mm
S1	18mm
Wire Size	0.8mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	100
Typical Component Weight	45 g

Specifications

Voltage AC	250 VAC
Inductance	20.3 mH
Rated Current	4 A
Temperature Range	-40/+120°C
DC Resistance	150 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.