



Click [here](#) for the 3D model.

Dimensions

D	25mm MAX
H	13mm MAX
LL	5mm +/-1mm
S	15mm
S1	15mm
Wire Size	0.85mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	10.3 g

General Information

Series	SC
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 35 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	0.6 mH (10 kHz)
Current	5 A
Temperature Range	-40/+120°C
DC Resistance	17.5 mOhms