



Click [here](#) for the 3D model.

#### General Information

Series	SC-J
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 65 K.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Inductance	4.2 mH (100 kHz)
Current	7 A
Temperature Range	-40/+120°C
DC Resistance	42 mOhms

#### Dimensions

D	34mm MAX
T	24mm MAX
H	33mm MAX
LL	4.5mm +/-1mm
S	18mm NOM
S1	16mm NOM
Wire Size	1.1mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	45.2 g