



Click [here](#) for the 3D model.

General Information

Series	SC-D
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 60 K.
Core	Ni-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	45 uH
Current	7 A
Temperature Range	-40/+105°C
DC Resistance	20 mOhms

Dimensions

D	24mm MAX
T	13.5mm MAX
LL	20mm +/-2mm
S	6mm
Wire Size	0.8mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	360
Typical Component Weight	9.3 g